

PRODUCT INFORMATION PACKET

Model No: 056T17D11047
Catalog No: K003A
1,1800,DP,56,3/60/208
Open Drip Proof (ODP)



Regal and Marathon are trademarks of Regal Beloit Corporation or one of its affiliated companies.
©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	1 Hp	Output KW	0.75 kW
Frequency	60 Hz	Voltage	208 V
Current	3.3 A	Speed	1725 rpm
Service Factor	1.15	Phase	3
Efficiency	83.5 %	Duty	Continuous
Insulation Class	B	Design Code	B
KVA Code	M	Frame	56
Enclosure	Drip Proof	Overload Protector	No
Ambient Temperature	40 °C	Drive End Bearing Size	6203
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	Y
IP Code	22		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid base	Motor Orientation	HORIZONTAL
Drive End Bearing	BALL	Opp Drive End Bearing	BALL
Frame Material	Rolled Steel	Shaft Type	T
Overall Length	11.72 in	Frame Length	5.75 in
Shaft Diameter	0.625 in	Shaft Extension	2.51 in
Assembly/Box Mounting	F1 OUT ODE BRKT RADIAL		
Outline Drawing	056T17D11047	Connection Diagram	D0000569-001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/30/2018

