

PRODUCT INFORMATION PACKET

Model No: 5KC39PN6200X
Catalog No: C1089A
3/4,3600,DP,1/60/115/230
Jet Pump



Regal and Marathon are trademarks of Regal Beloit Corporation or one of its affiliated companies.
©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	0.75 Hp	Output KW	0.56 kW
Frequency	60 Hz	Voltage	115/230 V
Current	13.0,6.5 A	Speed	3450 rpm
Service Factor	1.5	Phase	1
Efficiency	69.5 %	Duty	Continuous
Insulation Class	B	KVA Code	N
Frame	56J	Enclosure	Drip Proof
Overload Protector	AUTO	Ambient Temperature	50 °C
Drive End Bearing Size	6203	Opp Drive End Bearing Size	6203
UL	None	CE	N
IP Code	22		

Technical Specifications


Starting Method	SM	Poles	2
Rotation	Clockwise	Mounting	Round
Motor Orientation	ANY	Drive End Bearing	LOCKED
Opp Drive End Bearing	BALL	Frame Material	Rolled Steel
Overall Length	13.98 in	Frame Length	6.87 in
Shaft Diameter	0.63 in	Shaft Extension	1.89 in
Outline Drawing	52A107109P3	Connection Diagram	52A106889

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/30/2018



5	KC	32	56J	12.27	9.64		5.16
4	KC	39	56J	15.61	12.98		8.50
3	KC	39	56J	13.98	11.35		6.87
2	KC	33	56J	12.52	9.89		5.41
1	KC,KH	39	56J	11.54	8.91		4.43
P	TYPE	GE SIZE	NEMA FR	C	AG		SHELL REF.


				TOLERANCES UNLESS SPECIFIED		DRAWN MAM 02/09/91				
				DEC.	INCHES	CHK				
				.X	±.1	APPD MAM 06/05/91				
11	JET/POOL IS REPLACED BY JET PUMP PER ECO-0033464	PVR 05/15/13	DS	.XX	±.03	TITLE	OUTLINE	SCALE 3=8		
10	CHG TO RBC FORMAT PER ISO5-1777	AB 02/17/06		.XXX	±.005	2 COMPARTMENT UPGRADE - 56J - JET PUMP		REF		
9	ADDED PART #5	UJM 07/16/01		.XXXX	±.0005	MAT'L.		FMF		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2'	FINISH		PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		CAD FILE	52A107109	SIZE A	DRAWING NO. 52A107109	REV. 11
				DIST						




THIRD ANGLE PROJECTION

REV.	DESCRIPTION	DATE	APPROVED
2	UPDATED TO RBC FORMAT	01/11/06	MAM

SET ROTATION - DUAL VOLTAGE
TYPE KC OR KH WITH PROTECTOR



NOTE#1 - HI VOLTAGE SHOWN FOR LOW VOLTAGE
ROTATE VOLTAGE CHANGE PLUG TO LO POSITION.



CONNECTION LABEL - 52X333027

SIGNATURES	DATE
MODEL B.L.J.	07/21/92
DETAIL	
CHECKED	
ENGRG	
MFG	
QUALITY	
ISSUED B.L.J.	07/21/92
MATERIAL	SOLID MODEL: 52A106889



REGAL-BELOLT CORPORATION

REGAL-BELOLT CONNECTION DIAGRAM

TITLE

FMF: 2 COMPARTMENT DUAL VOLT, SET ROTATION

SIZE DRAWING A

SCALE: 1.000 REF. No.:

52A106889

REV 2

SHEET 1 of 1