











OPTIONS	Reference
LOCKING PIN FOR 2 PADLOCKS Ø 4 TO 8 mm (PADLOCKS NOT SUPPLIED)	
	Socket-outlet ref. +843
SAFETY HASP FOR UP TO 6 PADLOCKS	
	399A541
LARGER RELEASE BUTTON	
	Ref. socket +453
INLET CAP IP66/IP67	
	319A426
IP40 SELF RETURNING LID (MANUAL CLOSING)	
	Socket-outlet ref.+R


HANDLE	Input/ Cable outer Ø	Reference	Self-ejection
ELASTOMER HANDLE WITH GLAND			
	18-25 mm	555P0D25	Ref. +443
	25-35 mm	555P0D35	Ref. +443
	35-45 mm	555P0D45	Ref. +443
	45-49 mm	555P0D49	Ref. +443

POLY HANDLE + POLY CABLE GLAND			
	14-25 mm	515P032P	Ref. +443
	18-32 mm	515P040P	Ref. +443
	24-38 mm	515P050P	Ref. +443
	35-48 mm	515P063P	/



POLY HANDLE (WITHOUT CABLE GLAND)			
	M50	515P0M50	/
	M63	515P0M63	/

METAL HANDLE WITH METAL GLAND (+ EARTHING WIRE)			
	16-24 mm	595P032M	/
	22-32 mm	595P040M	/
	34-44 mm	595P050M	/
	35-48 mm	595P063M	/





METAL HANDLE METRIC THREAD ENTRY (WITHOUT CABLE GLAND)			
	M32	595P0M32	/
	M40	595P0M40	/
	M50	595P0M50	/
	M63	595P0M63	/


BOXES	△ x°	Input	Reference
METAL BOX (+ EARTHING WIRE) + POLY SLEEVE			
	30°	M32	515C3M32
	30°	M40	515C3M40
	30°	M50	515C3M50
	30°	M63	515C3M63

METAL BOX (+ EARTHING WIRE) + METAL SLEEVE			
	30°	M32	595C3M32
	30°	M40	595C3M40
	30°	M50	595C3M50
	30°	M63	595C3M63
	0° (Straight)	M32	595C0M32
	0° (Straight)	M40	595C0M40
	0° (Straight)	M50	595C0M50
	0° (Straight)	M63	595C0M63
	70°	M32	595C7M32
	70°	M40	595C7M40
70°	M50	595C7M50	
70°	M63	595C7M63	









METAL BOX (+ EARTHING WIRE) + METAL SLEEVE + CORNET			
	0° (Straight)	M50	595E0M50
	30°	M50	595E3M50
	30°	M63	595E3M63
	70°	M50	595E7M50
	70°	M63	595E7M63

Cable glands are not delivered with the boxes.

SLEEVE	△ x°	Reference
POLY SLEEVE		
	30°	515M3
METAL SLEEVE		
	0° (Straight)	595M0
	30°	595M3
	70°	595M7

OPTIONS	Reference		
LOCKING PIN FOR 2 PADLOCKS Ø 4 TO 8 mm (PADLOCKS NOT SUPPLIED)			
	Socket-outlet ref. +843		
SAFETY HASP FOR UP TO 6 PADLOCKS			
	399A541		
ALLEN-SCREW LOCKING LATCH			
Direct latch locking, no padlocking option.	Ref. socket + 22		
INLET CAP IP66/IP67			
	319A426		
IP40 SELF RETURNING LID (MANUAL CLOSING)			
	Socket-outlet ref.+R		
ELECTROMAGNETIC COMPATIBILITY (EMC) (SEE DETAIL PAGE 300)			
	Ref. socket and metal connector +EMC		
HANDLE	Input/ Cable outer Ø	Reference	EMC Option
ELASTOMER HANDLE WITH GLAND			
	18-25 mm	555P0D25	/
	25-35 mm	555P0D35	/
	35-45 mm	555P0D45	/
	45-49 mm	555P0D49	/
POLY HANDLE + POLY CABLE GLAND			
	14-25 mm	515P032P	/
	18-32 mm	515P040P	/
	24-38 mm	515P050P	/
	35-48 mm	515P063P	/
POLY HANDLE (WITHOUT CABLE GLAND)			
	M50	515P0M50	/
	M63	515P0M63	/
METAL HANDLE WITH METAL GLAND (+ EARTHING WIRE)			
	16-24 mm	595P032M	Ref. +EMC (11-21 mm)
	22-32 mm	595P040M	Ref. +EMC (19-28 mm)
	34-44 mm	595P050M	Ref. +EMC (27-35 mm)
	35-48 mm	595P063M	Ref. +EMC (34-45 mm)
METAL HANDLE METRIC THREAD ENTRY (WITHOUT CABLE GLAND)			
	M32	595P0M32	Ref. +EMC
	M40	595P0M40	Ref. +EMC
	M50	595P0M50	Ref. +EMC
	M63	595P0M63	Ref. +EMC

BOXES	∠x°	Input	Ref.	EMC Option
METAL BOX (+ EARTHING WIRE) + POLY SLEEVE				
	30°	M32	515C3M32	/
	30°	M40	515C3M40	/
	30°	M50	515C3M50	/
	30°	M63	515C3M63	/
METAL BOX (+ EARTHING WIRE) + METAL SLEEVE				
	30°	M32	595C3M32	Ref. +EMC
	30°	M40	595C3M40	Ref. +EMC
	30°	M50	595C3M50	Ref. +EMC
	30°	M63	595C3M63	Ref. +EMC
	0° (Straight)	M32	595C0M32	Ref. +EMC
	0° (Straight)	M40	595C0M40	Ref. +EMC
	0° (Straight)	M50	595C0M50	Ref. +EMC
	0° (Straight)	M63	595C0M63	Ref. +EMC
	70°	M32	595C7M32	Ref. +EMC
	70°	M40	595C7M40	Ref. +EMC
	70°	M50	595C7M50	Ref. +EMC
	70°	M63	595C7M63	Ref. +EMC
METAL BOX (+ EARTHING WIRE) + METAL SLEEVE + CORNET				
	0° (Straight)	M50	595E0M50	Ref. +EMC
	30°	M50	595E3M50	Ref. +EMC
	30°	M63	595E3M63	Ref. +EMC
	70°	M50	595E7M50	Ref. +EMC
	70°	M63	595E7M63	Ref. +EMC
Cable glands are not delivered with the boxes.				
SLEEVE	∠x°	Reference	EMC Option	
POLY SLEEVE				
	30°	515M3	/	
METAL SLEEVE				
	0° (Straight)	595M0	Ref. +EMC	
	30°	595M3	Ref. +EMC	
	70°	595M7	Ref. +EMC	

OPTIONS	Reference
LOCKING PIN FOR 3 PADLOCKS Ø 8 mm (PADLOCKS NOT SUPPLIED)	
	Ref. + 844
LARGER RELEASE BUTTON	
	Ref. socket + 453
INLET CAP	
	196A126
180° OPENING LID	
	Ref. socket + 10
IP40 SELF RETURNING LID (MANUAL CLOSING)	
	Socket-outlet ref.+R
180° OPENING + SELF-RETURNING LID	
	Ref. socket + 18
CLOSING MECHANISM	
	Draw lever only 196A376 Draw plate only 196A396
IP66/IP67 SOCKET-OUTLET AND INLET	
	Ref. + 600

HANDLE	Input/ Cable outer Ø	Reference
ELASTOMER HANDLE WITH GLAND		
	18-25 mm	555P0D25
	25-35 mm	555P0D35
	35-45 mm	555P0D45
	45-49 mm	555P0D49
POLY HANDLE + POLY CABLE GLAND		
	14-25 mm	515P032P
	18-32 mm	515P040P
	24-38 mm	515P050P
	35-48 mm	515P063P
	METAL HANDLE WITH METAL GLAND (+ EARTHING WIRE)	
	16-24 mm	595P032M
	22-32 mm	595P040M
	34-44 mm	595P050M
	35-48 mm	595P063M
	POLY HANDLE (WITHOUT CABLE GLAND)	
	M50	515P0M50
	M63	515P0M63
METAL HANDLE METRIC THREAD ENTRY (WITHOUT CABLE GLAND)		
	M32	595P0M32
	M40	595P0M40
	M50	595P0M50
	M63	595P0M63

BOXES	△x°	Input	Reference
METAL BOX (+ EARTHING WIRE) + POLY SLEEVE			
	30°	M32	515C3M32
	30°	M40	515C3M40
	30°	M50	515C3M50
	30°	M63	515C3M63
METAL BOX (+ EARTHING WIRE) + METAL SLEEVE			
	30°	M32	595C3M32
	30°	M40	595C3M40
	30°	M50	595C3M50
	30°	M63	595C3M63
	0° (Straight)	M32	595C0M32
	0° (Straight)	M40	595C0M40
	0° (Straight)	M50	595C0M50
	0° (Straight)	M63	595C0M63
	70°	M32	595C7M32
	70°	M40	595C7M40
	70°	M50	595C7M50
	70°	M63	595C7M63
METAL BOX (+ EARTHING WIRE) + METAL SLEEVE + CORNET			
	0° (Straight)	M50	595E0M50
	30°	M50	595E3M50
	30°	M63	595E3M63
	70°	M50	595E7M50
70°	M63	595E7M63	
Cable glands are not delivered with the boxes.			
SLEEVE	△x°	Reference	
POLY SLEEVE			
	30°	515M3	
METAL SLEEVE			
	0° (Straight)	595M0	
	30°	595M3	
	70°	595M7	