

DX9 Hazardous Location Plugs & Receptacles – 125 A

Devices rated for hazardous locations are not returnable.

Plug
(Male inlet w/handle) **or** **Inlet w/cap on box**
(Male)



North American Configurations

Voltage	Polarity	Part # Metal	Part # Metal
120 V	1P+N+G	26-91165	26-96165
125 V	1P+N+G	26-91075	26-96075
208 V	2P+G	26-91162	26-96162
208 V	3P+G	26-91163	26-96163
208 V	3P+N+G	26-91167	26-96167
250 V	2P+G	26-91072	26-96072
250 V	3P+G	26-91073	26-96073
250 V	2P+N+G	26-91076	26-96076
277 V	1P+N+G	26-91045	26-96045
480 V	2P+G	26-91042	26-96042
480 V	3P+G	26-91043-	26-96043
480 V	3P+N+G	26-91047	26-96047
600 V	3P+G	26-91143	26-96143

For international configurations (IEC/CE) visit meltric.com/international-catalog or contact Customer Service at 800-433-7642.

Ratings

- **Max Amperage & Voltage**
125 A, 750 VAC
- **Environmental Ratings**
IP65/IP66
- **Temperature Range**
Min -40°F / Max 140°F
See pg 266 for temps below -15°F.
- **Wiring Capacity**
Min 2 AWG Max 2/0 AWG
* Based on THHN wire sizes.
- **Applicable Standards**
ATEX, IECEx
- **Hazardous Location Ratings**

MARECHAL ELECTRIC MAROMME
II2 G/D Ex de IIC tD A21
-40°C ≤ Ta ≤ +60°C T5 T90°C
-40°C ≤ Ta ≤ +50°C T6 T80°C
IECEx LCI 09.0015/LCIE 04 ATEX 6038

Handle Cable Range

Suffix	Cable Range Size
-32M	.47" - .83"
None	.63" - .1.06"
-50M	.91" - 1.38"
-63M	1.42" - 1.89"

Box NPT Size

Suffix	NPT Thread Size
-1	1"
None	1 1/4"
-112	1 1/2"
-2	2"

NPT sizes are determined by the cable diameter and third party cord grip.

Accessories

Protective Cap



Metal Wall Box

NPT	Part #
1"	26-9A023-1
1 1/4"	26-9A023-114
1 1/2"	26-9A023-112
2"	26-9A023-2

Connector
(female recept w/handle) **or** **Receptacle on box**
(female) **or** **Receptacle**
(female)



North American Configurations

Voltage	Polarity	Part # Metal	Part # Metal	Part # Metal
120 V	1P+N+G	26-93165	26-90165	26-94165
125 V	1P+N+G	26-93075	26-90075	26-94075
208 V	2P+G	26-93162	26-90162	26-94162
208 V	3P+G	26-93163	26-90163	26-94163
208 V	3P+N+G	26-93167	26-90167	26-94167
250 V	2P+G	26-93072	26-90072	26-94072
250 V	3P+G	26-93073	26-90073	26-94073
250 V	2P+N+G	26-93076	26-90076	26-94076
277 V	1P+N+G	26-93045	26-90045	26-94045
480 V	2P+G	26-93042	26-90042	26-94042
480 V	3P+G	26-93043	26-90043	26-94043
480 V	3P+N+G	26-93047	26-90047	26-94047
600 V	3P+G	26-93143	26-90143	26-94143

For international configurations (IEC/CE) visit meltric.com/international-catalog or contact Customer Service at 800-433-7642.