


































OPTIONS	Reference
INDUSTRIAL/DOMESTIC ADAPTERS	
Industrial inlet MARECHAL® 1P+N+E and domestic socket-outlet 10/16A 230 V fuse protection 10A and 16A (with integrated fuse). All these plug adapters are available to local standards: replace D11 by D40 for UK, D30 for Germany/Netherlands/Luxembourg, D06 for Italy.	
	3118015D11
COUPLER FITTED WITH A DIFFERENTIAL BREAKER	
Coupler fitted with a domestic plug (IP44 - 10/16 A 250V 2P+E), a mobile socket-outlet (DS1 type - IP55-230V 1P+N+E) and a differential circuit breaker (IP55-10 or 30mA - nominal current 16A) with reset button.	
	3114015ID3 (30 mA)
LOCKING PIN FOR 2 PADLOCKS Ø 4 TO 8 mm (PADLOCK NOT SUPPLIED)	
	Socket-outlet ref. +843
SAFETY HASP FOR UP TO 6 PADLOCKS	
	613A541
LARGER RELEASE BUTTON	
	Ref. socket +453
INLET CAP IP66/IP67	
	311A426
IN-LINE CONNECTIONS (A PAIR OF FINGER DRAW PLATES TO AID CLOSING)	
	613A346
IP55 SELF-RETURNING LID	
	Socket-outlet ref.+R
IP55 METAL LOCKABLE SELF-CLOSING LID FOR INLET	
	311A226
SELF-EJECTING	
	See page 186
PRODUCTS AVAILABLE IN BLACK ●	
The black dot means these products are also available in black color. Replace the second character of the product reference with 5	

SLEEVE	Reference
POLY SLEEVE ●	
	30° 512M3
	70° 512M7
METAL SLEEVE	
	0° (Straight) 592M0
	30° 592M3

BOXES	Input	Reference
POLY BOX ●		
	30° M20	512B3M20
	30° M25	512B3M25
METAL BOX (+ EARTHING WIRE)		
	20° M20	592B2M20
	20° M25	592B2M25
POLY BOX + POLY SLEEVE		
	70° Without hole	512C7000
	70° Hole Ø 20	512C7M20
	70° Hole Ø 25	512C7M25
	70° Hole Ø 32	512C7M32
	70° Hole Ø 40	512C7M40
METAL BOX (+ EARTHING WIRE) + POLY SLEEVE		
	30° M20	512C3M20
	30° M25	512C3M25
	30° M32	512C3M32
	30° M40	512C3M40
METAL BOX (+ EARTHING WIRE) + METAL SLEEVE		
	30° M20	592C3M20
	30° M25	592C3M25
	30° M32	592C3M32
	0° (Straight) M20	592C0M20
	0° (Straight) M25	592C0M25
	0° (Straight) M32	592C0M32

Cable glands are not delivered with the boxes.

HANDLE	Input/ Cable outer Ø	Reference	Self-ejection
POLY HANDLE WITH GLAND ●			
	5-21 mm	512P0D21	/
POLY HANDLE + POLY CABLE GLAND ●			
	5-12 mm	512P020P	Ref. +443
	9-18 mm	512P025P	Ref. +443
	14-25 mm	512P032P	Ref. +443
	18-32 mm	512P040P	Ref. +443
POLY HANDLE (WITHOUT CABLE GLAND) ●			
	M20	512P0M20	Ref. +443
	M25	512P0M25	Ref. +443
	M32	512P0M32	Ref. +443
	M40	512P0M40	Ref. +443
METAL HANDLE WITH METAL GLAND (+ EARTHING WIRE)			
	7-13 mm	592P020M	/
	8-16 mm	592P025M	/
	16-24 mm	592P032M	/
METAL HANDLE METRIC THREAD ENTRY (WITHOUT CABLE GLAND)			
	M20	592P0M20	/
	M25	592P0M25	/
	M32	592P0M32	/

OPTIONS Reference

INDUSTRIAL/DOMESTIC ADAPTERS

Industrial inlet MARECHAL® 1P+N+E and domestic socket-outlet 10/16A 230 V fuse protection 10A and 16A (with integrated fuse).
All these plug adapters are available to local standards: replace D11 by D40 for UK, D30 for Germany/Netherlands/Luxembourg, D06 for Italy.



6138015D11

LOCKING PIN FOR 2 PADLOCKS Ø 4 TO 8 mm (PADLOCK NOT SUPPLIED)



Socket-outlet ref. +843

SAFETY HASP FOR UP TO 6 PADLOCKS



613A541

LARGER RELEASE BUTTON



Ref. socket +453

INLET CAP IP66/IP67



613A426

IN-LINE CONNECTIONS (A PAIR OF FINGER DRAW PLATES TO AID CLOSING)



613A346

180° OPENING LID



Ref. socket +10

IP40 SELF RETURNING LID (MANUAL CLOSING)



Socket-outlet ref.+R

180° OPENING + SELF-RETURNING LID



Ref. socket +18

IP55 METAL LOCKABLE SELF-CLOSING LID FOR INLET



613A226

SELF-EJECTION



See page 186

PRODUCTS AVAILABLE IN BLACK ●

The black dot means these products are also available in black color. Replace the second character of the product reference with 5

SLEEVE Reference

POLY SLEEVE ●



30°

512M3



70°

512M7

METAL SLEEVE



0° (Straight)

592M0



30°

592M3

BOXES Input Reference

POLY BOX ●



30°

M20

512B3M20

30°

M25

512B3M25

METAL BOX (+ EARTHING WIRE)



20°

M20

592B2M20

20°

M25

592B2M25

POLY BOX + POLY SLEEVE (BLACK VERSION SEE ACCESSORIES DXN3 PAGE 241)

70°

Without hole

512C7000

70°

Hole Ø 20

512C7M20

70°

Hole Ø 25

512C7M25

Earth bar ref.: 51AA089

70°

Hole Ø 32

512C7M32

70°

Hole Ø 40

512C7M40

METAL BOX (+ EARTHING WIRE) + POLY SLEEVE

30°

M20

512C3M20

30°

M25

512C3M25

30°

M32

512C3M32

30°

M40

512C3M40

METAL BOX (+ EARTHING WIRE) + METAL SLEEVE

30°

M20

592C3M20

30°

M25

592C3M25

30°

M32

592C3M32

0° (Straight)

M20

592C0M20

0° (Straight)

M25

592C0M25

0° (Straight)

M32

592C0M32

Cable glands are not delivered with the boxes.

HANDLE Input/
Cable outer Ø Reference Self-ejection

POLY HANDLE WITH GLAND ●



5-21 mm

512P0D21

/

POLY HANDLE + POLY CABLE GLAND ●

5-12 mm

512P020P

Ref. +443

9-18 mm

512P025P

Ref. +443

14-25 mm

512P032P

Ref. +443

18-32 mm

512P040P

Ref. +443

METAL HANDLE WITH METAL GLAND (+ EARTHING WIRE)

7-13 mm

592P020M

/

8-16 mm

592P025M

/

16-24 mm

592P032M

/

POLY HANDLE (WITHOUT CABLE GLAND) ●

M20

512P0M20

Ref. +443

M25

512P0M25

Ref. +443

M32

512P0M32

Ref. +443

M40

512P0M40

Ref. +443

METAL HANDLE METRIC THREAD ENTRY (WITHOUT CABLE GLAND)

M20

592P0M20

/

M25


592P0M25

/





M32









592P0M32

/
















OPTIONS	Reference
LOCKING PIN FOR 2 PADLOCKS Ø 4 TO 8 mm (PADLOCK NOT SUPPLIED)	
	Ref. + 843
LARGER RELEASE BUTTON	
	Ref. socket + 453
IN-LINE CONNECTIONS (A PAIR OF FINGER DRAW PLATES TO AID CLOSING)	
	613A346
INLET CAP IP66/IP67	
	613A426
180° OPENING LID	
	Ref. socket + 10
IP40 SELF RETURNING LID (MANUAL CLOSING)	
	Socket-outlet ref.+R
180° OPENING + SELF-RETURNING LID	
	Ref. socket + 18
BAG OF 13 FEMALES CONTACTS	
	01AA213
BAG OF 13 MALES CONTACTS	
	61CA113
PRODUCTS AVAILABLE IN BLACK ●	

The black dot means these products are also available in black color.
Replace the second character of the product reference with 5

SLEEVE	Reference
POLY SLEEVE ●	
	30° 512M3
	70° 512M7
METAL SLEEVE	
	0° (Straight) 592M0
	30° 592M3

BOXES	Input	Reference
POLY BOX ●		
	30° M20	512B3M20
	30° M25	512B3M25
METAL BOX (+ EARTHING WIRE)		
	20° M20	592B2M20
	20° M25	592B2M25
POLY BOX + POLY SLEEVE (BLACK VERSION SEE ACCESSORIES DXN3 PAGE 241)		
	70° Without hole	512C7000
	70° Ø 20 mm drill hole	512C7M20
	70° Ø 25 mm drill hole	512C7M25
	70° Ø 32 mm drill hole	512C7M32
	70° Ø 40 mm drill hole	512C7M40
Earth bar ref. : 51AA089		
METAL BOX (+ EARTHING WIRE) + POLY SLEEVE		
	30° M20	512C3M20
	30° M25	512C3M25
	30° M32	512C3M32
	30° M40	512C3M40
METAL BOX (+ EARTHING WIRE) + METAL SLEEVE		
	30° M20	592C3M20
	30° M25	592C3M25
	30° M32	592C3M32
	0° (Straight) M20	592C0M20
	0° (Straight) M25	592C0M25
	0° (Straight) M32	592C0M32

Cable glands are not delivered with the boxes.

HANDLE	Input/ Cable outer Ø	Reference
POLY HANDLE WITH GLAND ●		
	5-21 mm	512P0D21
POLY HANDLE + POLY CABLE GLAND ●		
	5-12 mm	512P020P
	9-18 mm	512P025P
	14-25 mm	512P032P
	18-32 mm	512P040P
METAL HANDLE WITH METAL GLAND (+ EARTHING WIRE)		
	7-13 mm	592P020M
	8-16 mm	592P025M
	16-24 mm	592P032M
POLY HANDLE (WITHOUT CABLE GLAND) ●		
	M20	512P0M20
	M25	512P0M25
	M32	512P0M32
	M40	512P0M40
METAL HANDLE METRIC THREAD ENTRY (WITHOUT CABLE GLAND)		
	M20	592P0M20
	M25	592P0M25
	M32	592P0M32