

SPARE PARTS



2





1

3

1

4

5

PLUG		DS1	DS3	DS6	DS9	DS2	DS4	
1	Plug interior	311A010	313A010	316A010	619A010	-	-	
1	Plug interior metal + E	-	-	396A110	699A110	392A110	394A110	
2	Locking ring	311A583	616A583	316A583	319A583	-	-	
2	Locking ring metal	-	-	396A583	399A583	392A583	394A583	
3	Plug contact (P or N)	311A011	616A011	316A011	619A011	392A011	394A011	
4	Color-coded voltage gasket		311AB26	313AB26	316AB26	319AB26	392AB26	-
		311AR26	313AR26	316AR26	319AR26	392AR26	-	
		311AV26	313AV26	-	-	-	-	
		311AN26	313AN26	316AN26	319AN26	392AN26	-	
5	Plug casing poly	311A501	313A501	316A501	619A501	-	-	
5	Plug casing metal	-	-	396A501	399A501	392A501	394A501	







REMEMBER TO ORDER THE SPECIAL REMOVAL KEY

Yellow disassembly key for poly casing
31-A500-1





SOCKET	DS1	DS3	DS6	DS9	DS2	DS4	
1 Socket Interior poly	311A020	313A020	316A020	619A020	-	-	
1 Socket Interior metal +E			396A220	699A220	392A220	394A220	
2 Locking ring	311A583	616A583	316A583	319A583	-	-	
2 Locking ring metal	-	-	396A583	399A583	392A583	394A583	
3 Socket contact (P or N)	311A021	616A021	316A021	619A021	392A021	394A021	
4 Color-coded voltage gasket		311AB26	313AB26	316AB26	319AB26	392AB26	-
		311AR26	313AR26	316AR26	319AR26	392AR26	-
		311AV26	313AV26	-	-	-	-
		311AN26	313AN26	316AN26	319AN26	392AN26	-
5 GRP socket casing	311A524*	313A524*	316A524*	619A524*	-	-	
5 Metal socket casing	-	-	396A524*	399A524*	392A524*	394A524*	
6 Lid gasket	311A563 (lid)	313A563 (lid)	396A074 (casing)	399A074 (metal) 619A074 (poly) (casing)	392A074 (casing)	394A074 (casing)	

*Add suffix cover option (opening 180°, self-returning, etc.).

CONTACT US FOR SPARE PARTS.