

# MILD STEEL BOXES with Ultra-Safe Fuse Holders

## Ratings

- Voltage**  
 20 A: 600 VAC  
 30 A: 600 VAC  
 60 A: 600 VAC
- Environmental Ratings**  
 Overall: NEMA Type 4  
 Box: NEMA Type 4, 12  
 Receptacle: NEMA Type 4X
- Temperature Range**  
 Min -40°F / Max 140°F  
 See pg 258 for temps below -15°F.
- Listings**  
 Box: UL 508A  
 Receptacle: UL 2682,  
 UL 1682, CSA 22.2 No. 182.1,  
 IEC 60309-1  
 Fuseholder: UL 512, IEC 269

## Standard Box



## Box with Viewing Window



## North American Configuration

| Voltage  | Polarity | Part #      |             |             | Part #       |              |              |
|----------|----------|-------------|-------------|-------------|--------------|--------------|--------------|
|          |          | 20 A        | 30 A        | 60 A        | 20 A         | 30 A         | 60 A         |
| 120V     | 1P+N+G   | FB-63-14165 | FB-63-34165 | FB-63-64165 | FBW-63-14165 | FBW-63-34165 | FBW-63-64165 |
| 120 208V | 3P+N+G   | FB-63-14167 | FB-63-34167 | FB-63-64167 | FBW-63-14167 | FBW-63-34167 | FBW-63-64167 |
| 125V     | 1P+N+G   | FB-63-14075 | FB-63-34075 | FB-63-64075 | FBW-63-14075 | FBW-63-34075 | FBW-63-64075 |
| 125 250V | 2P+N+G   | FB-63-14076 | FB-63-34076 | FB-63-64076 | FBW-63-14076 | FBW-63-34076 | FBW-63-64076 |
| 208V     | 2P+G     | FB-63-14162 | FB-63-34162 | FB-63-64162 | FBW-63-14162 | FBW-63-34162 | FBW-63-64162 |
| 208V     | 3P+G     | FB-63-14163 | FB-63-34163 | FB-63-64163 | FBW-63-14163 | FBW-63-34163 | FBW-63-64163 |
| 250V     | 2P+G     | FB-63-14072 | FB-63-34072 | FB-63-64072 | FBW-63-14072 | FBW-63-34072 | FBW-63-64072 |
| 250V     | 3P+G     | FB-63-14073 | FB-63-34073 | FB-63-64073 | FBW-63-14073 | FBW-63-34073 | FBW-63-64073 |
| 277V     | 1P+N+G   | FB-63-14045 | FB-63-34045 | FB-63-64045 | FBW-63-14045 | FBW-63-34045 | FBW-63-64045 |
| 277 480V | 3P+N+G   | FB-63-14047 | FB-63-34047 | FB-63-64047 | FBW-63-14047 | FBW-63-34047 | FBW-63-64047 |
| 347 600V | 3P+N+G   | FB-63-14147 | FB-63-34147 | FB-63-64147 | FBW-63-14147 | FBW-63-34147 | FBW-63-64147 |
| 480V     | 2P+G     | FB-63-14042 | FB-63-34042 | FB-63-64042 | FBW-63-14042 | FBW-63-34147 | FBW-63-64042 |
| 480V     | 3P+G     | FB-63-14043 | FB-63-34043 | FB-63-64043 | FBW-63-14043 | FBW-63-34042 | FBW-63-64043 |
| 600V     | 2P+G     | FB-63-14142 | FB-63-34142 | FB-63-64142 | FBW-63-14142 | FBW-63-34043 | FBW-63-64142 |
| 600V     | 3P+G     | FB-63-14143 | FB-63-34143 | FB-63-64143 | FBW-63-14143 | FBW-63-34142 | FBW-63-64143 |

## Main Options



**Auxiliary/Pilot Contacts**



**Mushroom Pawl**



**Padlock Pawl**



**Closed Lid Configuration**

Recommended for cord applications to keep lid tucked in to avoid damage.

## Receptacle Options

## Suffix #

|                                 |                       |
|---------------------------------|-----------------------|
| With 2 Auxiliary/Pilot Contacts | <b>Recept # - 972</b> |
| Mushroom Pawl                   | <b>Recept # - 375</b> |
| Padlock Pawl                    | <b>Recept # - 843</b> |
| Closed Lid Configuration        | <b>Recept # - NC</b>  |



30 A, 600V Ultra-Safe Fuse Holders for Class CC fuses are standard. They include a blown fuse indicator for each pole. Fuses are not included.

**!** See pages 235-244 for detailed information on these options