



# INSTALLATION ACCESSORIES – SIZE 2


Accessories rated for hazardous locations are not returnable.

**HANDLES**

HANDLE w/NPT		Part # Poly	Part # Metal
	1/2"	552P0N05	5K2P0N05
	3/4"	552P0N07	5K2P0N07
	1"	552P0N10	5K2P0N10
	1 1/4"	552P0N12	-

For available cord grips, see pg 168.

**POLY HANDLE w/Cable Range**


	.20 - .82"	552P0D21
---	------------	----------




Cable Range	NPT	Cable Range	NPT
.312 - .625"	1/2"	.660 - 1.000"	1"
.438 - .812"	3/4"	.875 - 1.375"	1 1/4"

NPT sizes are determined by the cable diameter and third party cord grip.


**BOXES**

POLY ANGLE WITH METAL BOX w/NPT			
	30°	1/2"	752C3N05
	30°	3/4"	752C3N07
	30°	1"	752C3N10
	30°	1 1/4"	752C3N12

\* 28.7 in<sup>3</sup> \* Interior volume with receptacle installed.

METAL ANGLE WITH METAL BOX w/NPT			
	30°	1/2"	7K2C3N05
	30°	3/4"	7K2C3N07
	30°	1"	7K2C3N10
	30°	1 1/4"	7K2C3N12


\* 28.7 in<sup>3</sup> \* Interior volume with receptacle installed.



POLY ANGLE WITH LARGER METAL BOX w/NPT			
	70°	1/2"	752C7N05
	70°	3/4"	752C7N07
	70°	1"	752C7N10
	70°	1 1/4"	752C7N12
	70°	1 1/2"	752C7N15

\* 75.0 in<sup>3</sup> \* Interior volume with receptacle installed.




NPT on top or bottom (if rotated). For other NPT configurations, contact customer service.

**ANGLES**

POLY ANGLE		
	30°	552M3

METAL ANGLE		
	0°	5K2M0
	30°	5K2M3

**MISCELLANEOUS ACCESSORIES**

<b>FINGER DRAWPLATES</b>		
	61-3A346	Set of Two (2) Recommended for easier connector closure.
<b>PROTECTIVE INLET/PLUG CAP</b>		
	31-1A426	For Intets/Plugs Only.
<b>RECEPTACLE LOCKING PIN</b>		
	LP-843	