



INSTALLATION ACCESSORIES – SIZE 4


Accessories rated for hazardous locations are not returnable.

HANDLES

HANDLE w/NPT	Part # Poly	Part # Metal
 Poly 1/2" 3/4" 1"	554P0N05	5K4P0N05
	554P0N07	5K4P0N07
	554P0N10	5K4P0N10
 Metal 1 1/4" 1 1/2"	554P0N12	5K4P0N12
	554P0N15	5K4P0N15

For available cord grips, see pg 168.

POLY HANDLE w/Cable Range

	.51 - 1.38"	554P0D35
---	-------------	----------

i


Cable Range	NPT	Cable Range	NPT
.312 - .625"	1/2"	.875 - 1.375"	1 1/4"
.438 - .812"	3/4"	.890 - 1.812"	1 1/2"
.660 - 1.000"	1"		

NPT sizes are determined by the cable diameter and third party cord grip.


BOXES

POLY ANGLE WITH METAL BOX w/NPT			
	30°	1"	754C3N10
	30°	1 1/4"	754C3N12
	30°	1 1/2"	754C3N15
	* 61.0 in ³	30°	2"

* Interior volume with receptacle installed.

METAL ANGLE WITH METAL BOX w/NPT			
	30°	1"	7K4C3N10
	30°	1 1/4"	7K4C3N12
	30°	1 1/2"	7K4C3N15
	* 59.4 in ³	30°	2"





* Interior volume with receptacle installed.

METAL ANGLE WITH METAL BOX w/NPT			
	70°	1"	7K4C7N10
	70°	1 1/4"	7K4C7N12
	70°	1 1/2"	7K4C7N15
	* 91.0 in ³	70°	2"





* Interior volume with receptacle installed.

NPT on top or bottom (if rotated). For other NPT configurations, contact customer service.

ANGLES

POLY ANGLE		
	30°	554M3
METAL ANGLE		
	0°	5K4M0
	30°	5K4M3
	70°	5K4M7

MISCELLANEOUS ACCESSORIES

FINGER DRAWPLATES		
	31-6A346	Set of Two (2) Recommended for easier connector closure.
PROTECTIVE INLET/PLUG CAP		
	31-6A426	For Inlets/Plugs Only.
PADLOCKABLE INLET/PLUG CAP		
	DS6MC	Aluminum – For Inlets/Plugs Only. -A155 suffix required to maintain water ingress protection.
RECEPTACLE LOCKING PIN		
	LP-843	

HAZARDOUS LOCATION