






INSTALLATION ACCESSORIES – SIZE 4


Unless indicated otherwise, accessories can be used with either poly or metal plugs and receptacles.


HANDLES

HANDLE w/NPT	Part # Poly	Part # Metal
 1/2"	514P0N05	594P0N05
 3/4"	514P0N07	594P0N07
 1"	514P0N10	594P0N10
 1 1/4"	514P0N12	594P0N12
 1 1/2"	514P0N15	594P0N15

For metal devices only


For available cord grips, see page 167.


POLY HANDLE w/CORD GRIP	Cable Range	Part #
	.680 - .980"	714P0DP4
	.980 - 1.260"	714P0EP4
	1.260 - 1.560"	714P0FP1

METAL HANDLE w/CORD GRIP	Cable Range	Part #
	.750 - .875"	794P0DS1
	.875 - 1.000"	794P0DS3
	1.000 - 1.125"	794P0ES2
	1.250 - 1.375"	794P0FS1
	1.438 - 1.562"	794P0FS2*
	1.562 - 1.688"	794P0FS3*


For metal devices only

*May require stripping of cable jacket.

POLY HANDLE	Cable Range	Part #
	.51 - 1.38"	514P0D35






POLY HANDLE w/BUILT IN DRAW GRIPS	Cable Range	Part #
	.51 - 1.38"	514P0D35473

Makes connector closures easier.


POLY HANDLE w/CLAMP & BUSHING	Cable Range	Part #
	1.250 - 1.375"	714P0S22
	1.438 - 1.562"	714P0S25
	1.562 - 1.688"	714P0S27
	1.688 - 1.812"	714P0S29

ANGLES

POLY ANGLE	Angle	Part # Poly	Part # Metal
	30°	514M3	514M7
	70°		Panel mounting only.

METAL ANGLE	Angle	Part #	Notes
	0°	594M0	
	30°	594M3	
	30°	794M3L	
	Oversized 30°	794M3	Mounts on oversize box only. Order with 715F0Nxx. See pg 50.
	70°	594M7	


BOXES


POLY CONDUIT ENTRY w/NPT	Angle	Size	Part #	Notes
	30°	1/2"	514B3N05	For poly devices only * Interior volume with receptacle installed.
	30°	3/4"	514B3N07	
	30°	1"	514B3N10	
	30°	1 1/4"	514B3N12	

* 27.7 in³


POLY WALL BOX w/ANGLE	Angle	Part #	Notes
	70°	514C7000	70° poly boxes are not drilled. Contact Customer Service if factory drilling is required. * Interior volume with receptacle installed.


* 181.24 in³

Ground Bar	Part #
	51AA089

POLY ANGLE WITH METAL BOX w/NPT	Angle	Size	Part #	Notes
	70°	1/2"	714C7N05	* Interior volume with receptacle installed.
	70°	3/4"	714C7N07	
	70°	1"	714C7N10	
	70°	1 1/4"	714C7N12	
	70°	1 1/2"	714C7N15	

* 177.7 in³


METAL BOX w/NPT	Angle	Size	Part #
	0°	1"	7T4F0N10
	0°	1 1/4"	7T4F0N12
	0°	1 1/2"	7T4F0N15
	0°	2"	7T4F0N20


POLY ANGLE WITH METAL BOX w/NPT	Angle	Size	Part #	Notes
	30°	1"	714C3N10	For metal angle, replace "71" prefix with "79". * Interior volume with receptacle installed.
	30°	1 1/4"	714C3N12	
	30°	1 1/2"	714C3N15	
	30°	2"	714C3N20	



* 61.0 in³ Poly Angle


* 59.4 in³ Metal Angle

MISCELLANEOUS ACCESSORIES

FINGER DRAWPLATES	Part #	Notes
	31-6A346	Set of Two (2) Recommended for cord to cord assembly applications, for easier connector closure.

PROTECTIVE INLET/PLUG CAP	Part #	Notes
	31-6A426	For Inlets/Plugs Only.

PADLOCKABLE INLET/PLUG CAP	Part #	Notes
	DS6PC	Poly – For Inlets/Plugs Only.
	DS6MC	Aluminum – For Inlets/Plugs Only. -A155 suffix required to maintain water ingress protection.

SPRING-LOADED PADLOCKABLE INLET/PLUG CAP	Part #	Notes
	31-6A226	For Poly Inlets/Plugs Only. -A155 suffix required to maintain water ingress protection.
	39-6A226	For Metal Inlets/Plugs Only.

RECEPTACLE LOCKING PIN	Part #	Notes
	LP-843	Requires Padlockable Pawl option (-843) on receptacle.