




INSTALLATION ACCESSORIES – SIZE 6


Unless indicated otherwise, accessories can be used with either poly or metal plugs and receptacles.


HANDLES

HANDLE w/NPT	Part # Poly	Part # Metal
 Poly 1"	516P0N10	596P0N10
1 1/4"	516P0N12	596P0N12
1 1/2"	516P0N15	596P0N15
 Metal 2"	516P0N20	596P0N20
2 1/2"	516P0N25	596P0N25
3" <small>For metal devices only</small>	-	596P0N30


For available cord grips, see page 167.

POLY HANDLE w/CORD GRIP	Cable Range	Part #
	1.520 - 1.860"	716P0GP2
	1.850 - 2.190"	716P0GP3*
	<small>*May require stripping of cable jacket.</small>	

METAL HANDLE w/CORD GRIP	Cable Range	Part #
	1.688 - 1.812"	796P0GS1
	1.812 - 1.938"	796P0GS2*
	1.938 - 2.062"	796P0JS1
	2.062 - 2.188"	796P0JS2
	2.188 - 2.312"	796P0JS3
	2.312 - 2.438"	796P0JS4*
	2.437 - 2.625"	796P0KS1
	2.625 - 2.812"	796P0KS2
	<small>*May require stripping of cable jacket.</small>	

METAL OVERSIZED HANDLE w/NPT	Part #
 1 1/2"	796P0N12
2"	796P0N15
2 1/2"	796P0N20
3"	796P0N25
3" <small>For metal devices only</small>	796P0N30

For available cord grips, see page 167.




SANTOPRENE HANDLE	Cable Range	Part #
	.984 - 1.378"	556P0D35
	1.378 - 1.772"	556P0D45
	1.772 - 1.929"	556P0D49

IP66/IP67

ANGLES






METAL ANGLE	Part #	Notes
 0°	596M0	
 Oversized 45°	796M4	Mounts on oversize metal box only. Order with 7T6F0N25XL.
 60°	596M6	
 Extended 60°	597M6	

BOXES

METAL ANGLE WITH METAL BOX w/NPT	Part #	Notes
 60° 1 1/2"	796C6N15	<small>* Interior volume with receptacle installed.</small>
60° 2"	796C6N20	
<small>* 248.4 in³</small> 60° 2 1/2"	796C6N25	
METAL BOX w/NPT	Part #	Notes
 0° 1 1/2"	7T6F0N15	<small>* Interior volume with receptacle installed.</small>
0° 2"	7T6F0N20	
0° 2 1/2"	7T6F0N25	
METAL OVERSIZED BOX w/NPT	Part #	Notes
 0° 2"	7T6F0N20XL	
0° 2 1/2"	7T6F0N25XL	
0° 3"	7T6F0N30XL	

NPT on top or bottom (if rotated). For other NPT configurations, contact customer service.

MISCELLANEOUS ACCESSORIES

PROTECTIVE INLET/PLUG CAP	Part #	Notes
	39-2A426	Covers lockout hole for watertight seal on inlet. Consult Customer Service for availability. For Inlets/Plugs Only.
PADLOCKABLE INLET/PLUG CAP	Part #	Notes
	DS2MC	Aluminum – For Inlets/Plugs Only. -A155 suffix required to maintain water ingress protection.
CORD GRIP with MESH	Part #	Notes
	see pg 167	
EASY RETROFIT ADAPTER PLATES	Part #	Notes
	see pg 164	Mount to existing boxes.
RECEPTACLE LOCKING PIN	Part #	Notes
	LP-843	Requires Padlockable Pawl option (-843) on receptacle.