





INSTALLATION ACCESSORIES – SIZE 1


HANDLES

HANDLE w/NPT		Part # Poly	Part # Metal
	Poly 1/2"	511P0N05	791P0N05L
	3/4"	511P0N07	791P0N07L
	Metal 1"	511P0N10	791P0N10L


For available cord grips, see page 167.

POLY HANDLE w/CORD GRIP		Cable Range	Part #
		.350 - .520"	711P0BP6
		.520 - .680"	711P0CP5
		.680 - .980"	711P0DP4


METAL HANDLE w/CORD GRIP		Cable Range	Part #
		.438 - .500"	791P0BS3L
		.500 - .562"	791P0BS4L
		.562 - .625"	791P0CS1L
		.625 - .750"	791P0CS4L

POLY HANDLE		Cable Range	Part #
		.35 - .70"	511P0D18


POLY EXTENDED HANDLE		Cable Range	Part #
		.20 - .83"	511P0D21


POLY ANGLED HANDLE		Cable Range	Part #
		.35 - .70"	511P6D18

ANGLES

POLY ANGLE		Part #	Notes
	MB Box 30°	511M3	


	70°	511M7	Panel mounting only.
---	-----	-------	----------------------

METAL ANGLE		Part #
	0°	591M0


	FS/FD Box 30°	791M3FS	* Base measures approximately 4.2" x 2.7". Due to the variation in sizes of FS boxes, please verify that your FS box matches our dimensions, if not call Customer Service for other solutions.
---	---------------	---------	--


	45°	591M4
---	-----	-------

BOXES


POLY CONDUIT ENTRY w/NPT		Part #	Notes
	30° 1/2"	511B3N05	* Interior volume with receptacle installed.
	30° 3/4"	511B3N07	

POLY WALL BOX w/ANGLE		Part #	Notes
	70°	511C7000	70° poly boxes are not drilled. Contact Customer Service if factory drilled is required.

	Ground Bar	51AA089	* Interior volume with receptacle installed.
---	------------	---------	--


POLY ANGLE WITH METAL BOX w/NPT		Part #	Notes
	70° 1/2"	711C7N05	* Interior volume with receptacle installed.
	70° 3/4"	711C7N07	
	70° 1"	711C7N10	
	70° 1 1/4"	711C7N12	
	70° 1 1/2"	711C7N15	


METAL BOX w/NPT		Part #
	0° 1/2"	7T1F0N05
	0° 3/4"	7T1F0N07
	0° 1"	7T1F0N10
	0° 1 1/4"	7T1F0N12

POLY ANGLE WITH METAL BOX w/NPT		Part #	Notes
	30° 1/2"	711C3N05	* Interior volume with receptacle installed.
	30° 3/4"	711C3N07	
	30° 1"	711C3N10	
	30° 1 1/4"	711C3N12	


NPT on top or bottom (if rotated). For other NPT configurations, contact Customer Service.

MISCELLANEOUS ACCESSORIES


FINGER DRAWPLATES		Part #	Notes
		61-1A346	Set of Two (2) Recommended for cord to cord assembly applications, for easier connector closure.

PROTECTIVE INLET/PLUG CAP		Part #	Notes
		61-1A426	For Inlets/Plugs Only.

PADLOCKABLE INLET/PLUG CAP		Part #	Notes
		61-1A826	For Inlets/Plugs Only.

SCREWDRIVER FOR TERMINAL SCREWS		Part #	Notes
		SD18	Klein 608-3 1/8" cabinet with 3" round shank.

EASY RETROFIT ADAPTER PLATES		Part #	Notes
		see pg 164	Mount to existing boxes.

RECEPTACLE LOCKING PIN		Part #	Notes
		LP-843	Requires Padlockable Pawl option (-843) on receptacle.