

# DX3 Hazardous Location Plugs & Receptacles – 32 A

Devices rated for hazardous locations are not returnable.

**Plug**  
(Male inlet w/handle)



or

**Inlet w/cap on box**  
(Male)



## North American Configurations

Voltage	Polarity	Part # Metal	Part # Metal
120V	1P+N+G	26-31165-XXX	26-36165-XX
125V	1P+N+G	26-21075-XXX	26-26075-XX
208V	2P+G	26-31162-XXX	26-36162-XX
208V	3P+G	26-21163-XXX	26-26163-XX
208V	3P+N+G	26-31167-XXX	26-36167-XX
250V	2P+G	26-21072-XXX	26-26072-XX
250V	3P+G	26-31073-XXX	26-36073-XX
250V	2P+N+G	26-21076-XXX	26-26076-XX
277V	1P+N+G	26-31045-XXX	26-36045-XX
480V	2P+G	26-21042-XXX	26-26042-XX
480V	3P+G	26-31043-XXX	26-36043-XX
480V	3P+N+G	26-21047-XXX	26-26047-XX
600V	3P+G	26-31143-XXX	26-36143-XX

### Ratings

- **Max Amperage & Voltage**  
32 A, 750 VAC
- **Environmental Ratings**  
IP65
- **Temperature Range**  
Min -13°F/ Max 140°F  
See pg 258 for temps below -15°F.
- **Wiring Capacity**  
Min 14 AWG Max 8 AWG  
\* Based on THHN wire sizes
- **Applicable Standards**  
ATEX, IECEx
- **Hazardous Location Ratings**

MARECHAL ELECTRIC MAROMME  
II2 G/D Ex de IIC tD A21  
-25°C ≤ Ta ≤ +60°C T5 T84°C  
-25°C ≤ Ta ≤ +50°C T6 T74°C  
IECEx LCI 09.0014/LCIE 05 ATEX 6127

### XXX Suffix/ Cable Range

XXX (Suffix #)	Cable Range
-25M	.35" - .63"
-32M	.47" - .83"

**Connector**  
(female recept w/handle)



or

**Receptacle on box**  
(female)



or

**Receptacle**  
(female)



## North American Configurations

Voltage	Polarity	Part # Metal	Part # Metal	Part # Metal
120V	1P+N+G	26-33165-XXX	26-30165-XX	26-34165
125V	1P+N+G	26-33075-XXX	26-30075-XX	26-34075
208V	2P+G	26-33162-XXX	26-30162-XX	26-34162
208V	3P+G	26-33163-XXX	26-30163-XX	26-34163
208V	3P+N+G	26-33167-XXX	26-30167-XX	26-34167
250V	2P+G	26-33072-XXX	26-30072-XX	26-34072
250V	3P+G	26-33073-XXX	26-30073-XX	26-34073
250V	2P+N+G	26-33076-XXX	26-30076-XX	26-34076
277V	1P+N+G	26-33045-XXX	26-30045-XX	26-34045
480V	2P+G	26-33042-XXX	26-30042-XX	26-34042
480V	3P+G	26-33043-XXX	26-30043-XX	26-34043
480V	3P+N+G	26-33047-XXX	26-30047-XX	26-34047
600V	3P+G	26-33143-XXX	26-30143-XX	26-34143

### XX Suffix/ NPT Size

NPT Thread Size	XX (Suffix #)
1/2"	-12
3/4"	-34
1"	-1

NPT sizes are determined by the cable diameter and third party cord grip.

### Accessories

#### Protective Cap



For Male Devices Only

DX3

26-3A126

#### Metal Wall Box



NPT

Part #

1/2"

26-3A023-12

3/4"

26-3A023-34

1"

26-3A023-1