

DX6 Hazardous Location Plugs & Receptacles – 63 A

Devices rated for hazardous locations are not returnable.

Ratings

- **Max Amperage & Voltage** 63 A, 750 VAC
- **Environmental Ratings** IP65/IP66
- **Temperature Range** Min -40°F / Max 140°F
See pg 258 for temps below -15°F.
- **Wiring Capacity** Min 6 AWG Max 1/0 AWG
* Based on THHN wire sizes
- **Applicable Standards** ATEX, IECEx
- **Hazardous Location Ratings**

MARECHAL ELECTRIC MAROMME
II2 G/D Ex de IIC tD A21
-40°C ≤ Ta ≤ +60°C T5 T90°C
-40°C ≤ Ta ≤ +50°C T6 T80°C
IECEx LCI 09.0015/LCIE 04 ATEX 6038

XXX Suffix/Cable Range

XXX (Suffix #)	Cable Range
-32M	.47" - .83"
-40M	.63" - 1.06"

XX Suffix/NPT Size

NPT Thread Size	XX (Suffix #)
1"	-1
1 1/4"	-114
1 1/2"	-112
2"	-2

NPT sizes are determined by the cable diameter and third party cord grip.

Accessories

Protective Cap



For Male Devices Only

DX6 26-6A126

Metal Wall Box



NPT	Part #
1"	26-6A023-1
1 1/4"	26-6A023-114
1 1/2"	26-6A023-112
2"	26-6A023-2

Plug
(Male inlet w/handle)



Inlet w/cap on box
(Male)



or

North American Configurations

Voltage	Polarity	Part #	
		Metal	Metal
120V	1P+N+G	26-61165-XXX	26-66165-XX
125V	1P+N+G	26-61075-XXX	26-66075-XX
208V	2P+G	26-61162-XXX	26-66162-XX
208V	3P+G	26-61163-XXX	26-66163-XX
208V	3P+N+G	26-61167-XXX	26-66167-XX
250V	2P+G	26-61072-XXX	26-66072-XX
250V	3P+G	26-61073-XXX	26-66073-XX
250V	2P+N+G	26-61076-XXX	26-66076-XX
277V	1P+N+G	26-61045-XXX	26-66045-XX
480V	2P+G	26-61042-XXX	26-66042-XX
480V	3P+G	26-61043-XXX	26-66043-XX
480V	3P+N+G	26-61047-XXX	26-66047-XX
600V	3P+G	26-61143-XXX	26-66143-XX

Connector
(female recept w/handle)



Receptacle on box
(female)



Receptacle
(female)



or

or

North American Configurations

Voltage	Polarity	Part #		
		Metal	Metal	Metal
120V	1P+N+G	26-63165-XXX	26-60165-XX	26-64165
125V	1P+N+G	26-63075-XXX	26-60075-XX	26-64075
208V	2P+G	26-63162-XXX	26-60162-XX	26-64162
208V	3P+G	26-63163-XXX	26-60163-XX	26-64163
208V	3P+N+G	26-63167-XXX	26-60167-XX	26-64167
250V	2P+G	26-63072-XXX	26-60072-XX	26-64072
250V	3P+G	26-63073-XXX	26-60073-XX	26-64073
250V	2P+N+G	26-63076-XXX	26-60076-XX	26-64076
277V	1P+N+G	26-63045-XXX	26-60045-XX	26-64045
480V	2P+G	26-63042-XXX	26-60042-XX	26-64042
480V	3P+G	26-63043-XXX	26-60043-XX	26-64043
480V	3P+N+G	26-63047-XXX	26-60047-XX	26-64047
600V	3P+G	26-63143-XXX	26-60143-XX	26-64143