

# PN12c Multipin Plugs & Receptacles – 7.5 A

## Ratings

- **Voltage**  
600 VAC Max / 130 VDC
- **Amperage Rating**  
2 A Current Interrupting  
7.5 A Non-Current Interrupting  
! PN12c is capable of handling 4-20mA low current applications
- **Environmental Ratings**  
IP66/IP67 (Poly & Metal)+
- **Temperature Range**  
Min -40°F / Max 140°F  
See pg 258 for temps below -15°F.
- **Wiring Capacity**  
Min 18 AWG Max 14 AWG

\* Does not apply to stainless steel version.

## Receptacle (female)



## Inlet (male)



**!** Don't forget to add installation accessories to your order

## North American Configurations

Voltage	Polarity	Part #			Part #		
		Poly	Metal	Stainless Steel	Poly	Metal	Stainless Steel
<b>600V</b>	11P+G	03-A4001	07-A4001	07-A4001-SS	03-A8001	07-A8001	07-A8001-SS

## Main Options



**Reverse Interiors**



**Flush Mount**  
(replaces female casing)



**Locking Pawl**

## Receptacle Options

## Suffix #

## Inlet Options

## Suffix #

Reverse Interiors

**Recept # - 001**

Reverse Interiors

**Inlet # - 001**

With Flush Mount (poly only)

**Recept # - 142\***

Locking Pawl

**Recept # - 824-300**

\* IP55 rating with Flush Mount casing



**!** See pages 235-244 for detailed information on these options

**Order Example: 600V PN12c + Reverse Interiors**  
PN12c Receptacle 11P+G = 03-A4001-001


# INSTALLATION ACCESSORIES – SIZE 1


Unless indicated otherwise, accessories can be used with either poly or metal plugs and receptacles. Stainless steel devices should use stainless steel accessories.


**HANDLES**


HANDLE w/NPT		Part # Poly	Part # Metal
	1/2"	511P0N05	591P0N05
	3/4"	511P0N07	591P0N07
	1"	511P0N10	591P0N10

For available cord grips, see pg 167.

POLY HANDLE w/CORD GRIP	Cable Range	Part #
	.350 - .520"	711P0BP6
	.520 - .680"	711P0CP5
	.680 - .980"	711P0DP4

METAL HANDLE w/CORD GRIP	Cable Range	Part #
	.438 - .500"	791P0BS3
	.500 - .562"	791P0BS4
	.562 - .625"	791P0CS1
	.625 - .750"	791P0CS4
	.750 - .875"	791P0DS1
	.875 - 1.000"	791P0DS3

POLY 90° HANDLE w/NPT		Part #
	1/2"	751P9N05
	3/4"	751P9N07
	1"	751P9N10


STAINLESS STEEL HANDLE w/NPT		Part #
	1/2"	7X1P0N05
	3/4"	7X1P0N07
	1"	7X1P0N10

For Stainless Steel devices only. For 1/2" NPT size, a hole size reducer is utilized.


POLY HANDLE	Cable Range	Part #
	.35 - .70"	511P0D18

POLY ANGLED HANDLE	Cable Range	Part #
	.35 - .70"	511P6D18

**ANGLES**

POLY ANGLE		Part #
	MB Box 30°	511M3
	70°	511M7


METAL ANGLE		Part #
	0°	591M0


FS/FD Box 30°		Part #	Notes
		791M3FS	* Base measures approximately 4.2" x 2.7". Due to the variation in sizes of FS boxes, please verify that your FS box matches our dimensions, if not call Customer Service for other solutions.

45°		Part #
		591M4



STAINLESS STEEL ANGLE		Part #	Notes
	30°	7X1M4	For Stainless Steel devices only.


**BOXES**


POLY CONDUIT ENTRY w/NPT		Part #	Notes
	30° 1/2"	511B3N05	* Interior volume with receptacle installed.
	30° 3/4"	511B3N07	


POLY WALL BOX w/NPT		Part #	Notes
	0° 1/2"	511B0N05	* Interior volume with receptacle installed.
	0° 3/4"	511B0N07	


METAL WALL BOX w/NPT		Part #	Notes
	0° 1/2"	591B0N05	* Interior volume with receptacle installed.
	0° 3/4"	591B0N07	

POLY WALL BOX w/ANGLE		Part #	Notes
	70°	511C7000	70° poly boxes are not drilled. Contact customer service if factory drilled is required.
	Ground Bar	51AA089	* Interior volume with receptacle installed.

METAL BOX w/NPT		Part #
	0° 1/2"	7T1F0N05
	0° 3/4"	7T1F0N07
	0° 1"	7T1F0N10
	0° 1 1/4"	7T1F0N12


POLY ANGLE WITH METAL BOX w/NPT		Part #	Notes
	30° 1/2"	711C3N05	* Interior volume with receptacle installed.
	30° 3/4"	711C3N07	
	30° 1"	711C3N10	
	30° 1 1/4"	711C3N12	

METAL ANGLE WITH METAL BOX w/NPT		Part #	Notes
	45° 1/2"	791C4N05	* Interior volume with receptacle installed.
	45° 3/4"	791C4N07	
	45° 1"	791C4N10	
	45° 1 1/4"	791C4N12	

STAINLESS STEEL BOX WITH STAINLESS STEEL ANGLE w/NPT		Part #	Notes
	30° 3/4"	7X1C3N07	* Includes angle adapter as shown. For Stainless Steel devices only.
	30° 1"	7X1C3N10	

**MISCELLANEOUS ACCESSORIES**

PROTECTIVE INLET/PLUG CAP		Part #	Notes
	01-NA426	For Inlets/Plugs Only.	

FLUSH MOUNT		Part #
	01-2A142	

CORD GRIP with MESH		Notes
	see pg 167	

MULTI-CONTACT REMOVAL TOOL		Part #
	61-CA593	

CRIMPER TOOL (GREENLEE OR EQUAL)		Part #
	4CN30	

EUROPEAN CRIMPING TOOL		Part #
	61-CA500	

MULTIPIN