



PN20 INLET

01-N8072

SPECIFICATIONS

20 A

250 VAC

Type 4X

Rated Current (A)	20 A
Rated Voltage (V)	250 VAC
Contact Configuration	2P+G
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	Type 4X IP 66/67
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG – 8 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 182.1-07
Accessory Size	1
Base Drawing Number	01-n8xxx.pdf
Catalog	meltric-catalog-pn-en.pdf