



PN7c RECEPTACLE

03-P4041-824-300

SPECIFICATIONS

15 A

480 VAC

IP66/IP67

Rated Current (A)	15 A
Rated Voltage (V)	480 VAC
Contact Configuration	4P+G
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	IP 66/67
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	18 AWG – 10 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 94.2-15
Option(1)	SCREW TYPE LOCKING PAWL
Accessory Size	1
Base Drawing Number	01-p40x1.pdf
Catalog	meltric-catalog-pn7c-en.pdf