



PN20 RECEPTACLE

09-N4073-824-300-LC

SPECIFICATIONS

20 A

250 VAC

Type 4X or IP66/IP67

Rated Current (A)	20 A
Rated Voltage (V)	250 VAC
Contact Configuration	3P+G
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	IP 66/67
Impact Rating	IK09
Material	METAL
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG – 8 AWG SCREW TERMINAL
Applicable Standards	cCSAus
Option(1)	LESS COVER
Option(2)	SCREW TYPE LOCKING PAWL
Accessory Size	1
Base Drawing Number	09-n4xxx.pdf
Catalog	meltric-catalog-pn-en.pdf