



# DX3 RECEPTACLE/BOX

26-30043

## SPECIFICATIONS

30 A

480 VAC

IP65

<b>Rated Current (A)</b>	30 A
<b>Rated Voltage (V)</b>	480 VAC
<b>Contact Configuration</b>	3P+G
<b>Ratings Information</b>	CURRENT INTERRUPTING
<b>Environmental Rating</b>	IP 65
<b>Short Circuit Rating</b>	10 kA - CLOSE & WITHSTAND
<b>Impact Rating</b>	IK10
<b>Material</b>	METAL
<b>Metal Type</b>	ALUMINUM PAINTED
<b>Product Color</b>	BLACK
<b>Thread Size</b>	1" NPT
<b>Cable Range</b>	.750-1.000"
<b>Minimum Operating Temperature</b>	-13F -25C
<b>Maximum Operating Temperature</b>	140F 60C
<b>Wiring Capacity - Phase Contacts</b>	14 AWG – 8 AWG SCREW TERMINAL
<b>Hazardous Ratings</b>	Zone 1 & 2 Gb T5-T6 Zone 21 & 22 tD T74C-T84C
<b>Accessory Size</b>	8
<b>Base Drawing Number</b>	<a href="#">26-30xxx-xx.PDF</a>
<b>Catalog</b>	<a href="#">meltric-catalog-dx1-en.pdf</a>