



DX3 CONNECTOR

26-33143

SPECIFICATIONS

30 A

600 VAC

IP65

Rated Current (A)	30 A
Rated Voltage (V)	600 VAC
Contact Configuration	3P+G
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	IP 65
Short Circuit Rating	10 kA - CLOSE & WITHSTAND
Impact Rating	IK10
Material	METAL
Metal Type	ALUMINUM PAINTED
Product Color	BLACK
Thread Size	M25
Cable Range	.350-.630"
Minimum Operating Temperature	-13F -25C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG - 8 AWG SCREW TERMINAL
Hazardous Ratings	Zone 1 & 2 Gb T5-T6 Zone 21 & 22 tD T74C-T84C
Accessory Size	8
Base Drawing Number	26-33xxx-xxx.PDF
Catalog	meltric-catalog-dx3-en.pdf