



DX6 PLUG

26-61165

SPECIFICATIONS

60 A

120 VAC

IP65

Rated Current (A)	60 A
Rated Voltage (V)	120 VAC
Contact Configuration	1P+N+G
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	IP 65
Short Circuit Rating	10 kA - CLOSE & WITHSTAND
Impact Rating	IK10
Material	METAL
Metal Type	ALUMINUM PAINTED
Product Color	BLACK
Thread Size	M32
Cable Range	.470-.830"
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	6 AWG - 1/0 AWG SCREW TERMINAL
Hazardous Ratings	Zone 1 & 2 Gb T5-T6 Zone 21 & 22 tD T74C-T84C
Accessory Size	9
Base Drawing Number	26-61xxx-xxx.pdf
Catalog	meltric-catalog-dx6-en.pdf