



DR30 RECEPTACLE

31-14173-K07-972

SPECIFICATIONS

30 A

250 VAC

Type 3R

Rated Current (A)	30 A
Rated Voltage (V)	250 VAC
Contact Configuration	3P+G
Auxiliary Contacts	+2 AUX
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	Type 3R IP 55
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG - 8 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	2
Base Drawing Number	31-14xxx-kxx.PDF
Catalog	meltric-catalog-dr30-en.pdf