



# DR30 RECEPTACLE

31-14183-K14-843

## SPECIFICATIONS

30 A

600 VAC

Type 3R

<b>Rated Current (A)</b>	30 A
<b>Rated Voltage (V)</b>	600 VAC
<b>Contact Configuration</b>	3P+G
<b>Ratings Information</b>	NON-CURRENT INTERRUPTING
<b>Environmental Rating</b>	Type 3R IP 55
<b>Short Circuit Rating</b>	100 kA - CLOSE & WITHSTAND
<b>Impact Rating</b>	IK09
<b>Material</b>	POLY
<b>Product Color</b>	BLUE
<b>Minimum Operating Temperature</b>	-40F -40C
<b>Maximum Operating Temperature</b>	140F 60C
<b>Wiring Capacity - Phase Contacts</b>	14 AWG - 8 AWG SCREW TERMINAL
<b>Applicable Standards</b>	UL 1682 cCSAus C22.2 No. 182.1-13
<b>Option(1)</b>	PADLOCK PAWL
<b>Accessory Size</b>	2
<b>Base Drawing Number</b>	<a href="#">31-14xxx-kxx.PDF</a>
<b>Catalog</b>	<a href="#">meltric-catalog-dr30-en.pdf</a>