



DR50 INLET

31-38172-K07-972

SPECIFICATIONS

50 A

250 VAC

Type 3R

Rated Current (A)	50 A
Rated Voltage (V)	250 VAC
Contact Configuration	2P+G
Auxiliary Contacts	+2 AUX
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	Type 3R IP 54
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG – 4 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	3
Base Drawing Number	31-38xxx-kxx.PDF
Catalog	meltric-catalog-dr50-en.pdf