



DS20 RECEPTACLE

33-14047-843

SPECIFICATIONS

20 A
 277/480 VAC
 Type 3R
 2 hp/7.5 hp

Rated Current (A)	20 A
Rated Voltage (V)	277/480 VAC
Horsepower Rating	2 hp/7.5 hp
Contact Configuration	3P+N+G
Auxiliary Contacts	NO AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 3R IP 55
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG - 8 AWG SCREW TERMINAL
Applicable Standards	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
Option(1)	PADLOCK PAWL
Accessory Size	2
Base Drawing Number	33-14xxx.PDF
Catalog	meltric-catalog-ds20-en.pdf