



# DS20 RECEPTACLE

## 33-14047-NC

### SPECIFICATIONS

20 A

277/480 VAC

Type 3R

2 hp/7.5 hp

<b>Rated Current (A)</b>	20 A
<b>Rated Voltage (V)</b>	277/480 VAC
<b>Horsepower Rating</b>	2 hp/7.5 hp
<b>Contact Configuration</b>	3P+N+G
<b>Auxiliary Contacts</b>	NO AUX
<b>Ratings Information</b>	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
<b>Environmental Rating</b>	Type 3R IP 55
<b>Short Circuit Rating</b>	100 kA - CLOSE & WITHSTAND
<b>Impact Rating</b>	IK09
<b>Material</b>	POLY
<b>Product Color</b>	BLUE
<b>Minimum Operating Temperature</b>	-40F -40C
<b>Maximum Operating Temperature</b>	140F 60C
<b>Wiring Capacity - Phase Contacts</b>	14 AWG – 8 AWG SCREW TERMINAL
<b>Applicable Standards</b>	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
<b>Option(1)</b>	NORMALLY CLOSED LID
<b>Accessory Size</b>	2
<b>Base Drawing Number</b>	<a href="#">33-14xxx.PDF</a>
<b>Catalog</b>	<a href="#">meltric-catalog-ds20-en.pdf</a>