



DS100 RECEPTACLE

33-94165

SPECIFICATIONS

100 A
 120 VAC
 Type 4X
 3 hp

Rated Current (A)	100 A
Rated Voltage (V)	120 VAC
Horsepower Rating	3 hp
Contact Configuration	1P+N+G
Auxiliary Contacts	NO AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 4X IP 66/67
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	4 AWG - 2/0 AWG SCREW TERMINAL
Applicable Standards	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	5
Base Drawing Number	33-94xxx.PDF
Catalog	meltric-catalog-ds100-en.pdf