



DS20 RECEPTACLE

33-14076-352

SPECIFICATIONS

20 A

125/250 VAC

Type 3R

0.75 hp/2 hp

Rated Current (A)	20 A
Rated Voltage (V)	125/250 VAC
Horsepower Rating	0.75 hp/2 hp
Contact Configuration	2P+N+G
Auxiliary Contacts	NO AUX
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	Type 3R IP 55
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG – 8 AWG SCREW TERMINAL
Applicable Standards	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
Option(1)	STRAIGHT INSERTION
Accessory Size	2
Base Drawing Number	33-14xxx.PDF
Catalog	meltric-catalog-ds20-en.pdf