



DSDC1 HAZ RECEPTACLE

35-14209-HAZ

SPECIFICATIONS

20 A

250 VDC

Type 4X

Rated Current (A)	20 A
Rated Voltage (V)	250 VDC
Contact Configuration	2P+G
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	Type 4X
Impact Rating	IK09
Material	POLY
Product Color	BLACK
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	104F 40C
Wiring Capacity - Phase Contacts	14 AWG – 8 AWG SCREW TERMINAL
Applicable Standards	cCSAus C22.2 No. 182.1-07
Accessory Size	2
Base Drawing Number	35-14209-xxx-haz.pdf
Catalog	meltric-catalog-zone2-dsdc-en.pdf