



# DS20 HAZ INLET

35-18073-972-HAZ

## SPECIFICATIONS

20 A  
250 VAC  
Type 4X  
5 hp

<b>Rated Current (A)</b>	20 A
<b>Rated Voltage (V)</b>	250 VAC
<b>Horsepower Rating</b>	5 hp
<b>Contact Configuration</b>	3P+G
<b>Auxiliary Contacts</b>	+2 AUX
<b>Ratings Information</b>	NON-CURRENT INTERRUPTING
<b>Environmental Rating</b>	Type 4X
<b>Short Circuit Rating</b>	100 kA - CLOSE & WITHSTAND
<b>Impact Rating</b>	IK09
<b>Material</b>	POLY
<b>Product Color</b>	BLACK
<b>Minimum Operating Temperature</b>	-40F -40C
<b>Maximum Operating Temperature</b>	104F 40C
<b>Wiring Capacity - Phase Contacts</b>	14 AWG – 8 AWG SCREW TERMINAL
<b>Applicable Standards</b>	cCSAus C22.2 No. 182.1-07
<b>Accessory Size</b>	2
<b>Base Drawing Number</b>	<a href="#">35-18xxx-xxx-haz.PDF</a>
<b>Catalog</b>	<a href="#">meltric-catalog-zone2-ds20-en.pdf</a>