



DSDC9 HAZ INLET

36-98109-HAZ

SPECIFICATIONS

100 A

130 VDC

Type 4X

Rated Current (A)	100 A
Rated Voltage (V)	130 VDC
Contact Configuration	2P+G
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	Type 4X IP 66/67
Impact Rating	IK10
Material	METAL
Metal Type	ZAMAK
Product Color	METAL
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	104F 40C
Wiring Capacity - Phase Contacts	4 AWG - 2/0 AWG SCREW TERMINAL
Applicable Standards	cCSAus C22.2 No. 182.1-07
Accessory Size	5
Base Drawing Number	36-98109-xxx-haz.pdf
Catalog	meltric-catalog-zone2-dsdc-en.pdf