



DS200 INLET

37-28043-976

SPECIFICATIONS

200 A
 480 VAC
 Type 4X
 100 hp

Rated Current (A)	200 A
Rated Voltage (V)	480 VAC
Horsepower Rating	100 hp
Contact Configuration	3P+G
Auxiliary Contacts	+6 AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 4X IP 66/67
Short Circuit Rating	10 kA - CLOSE & WITHSTAND
Impact Rating	v
Material	METAL
Metal Type	ALUMINUM
Product Color	METAL
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	4 AWG – 4/0 AWG SCREW TERMINAL
Applicable Standards	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	6
Base Drawing Number	37-28xxx.PDF
Catalog	meltric-catalog-ds200-en.pdf