



DR250 INLET

39-28247-K04-A155

SPECIFICATIONS

250 A

277/480 VAC

Type 4X

Rated Current (A)	250 A
Rated Voltage (V)	277/480 VAC
Contact Configuration	3P+N+G
Auxiliary Contacts	NO AUX
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	Type 4X IP 66/67
Short Circuit Rating	10 kA - CLOSE & WITHSTAND
Impact Rating	IK10
Material	METAL
Metal Type	ALUMINUM
Product Color	METAL
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	4 AWG – 4/0 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 182.1-13
Option(1)	WITH NO LOCKOUT HOLE
Accessory Size	6
Base Drawing Number	39-28xxx-kxx.PDF
Catalog	meltric-catalog-dr250-en.pdf