



DR150 RECEPTACLE

39-94242-K04

SPECIFICATIONS

150 A

480 VAC

Type 4X & IP69

Rated Current (A)	150 A
Rated Voltage (V)	480 VAC
Contact Configuration	2P+G
Auxiliary Contacts	NO AUX
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK10
Material	METAL
Metal Type	ALUMINUM
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	4 AWG – 2/0 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	5
Base Drawing Number	39-94xxx-kxx.PDF
Catalog	meltric-catalog-dr150-en.pdf