



SP RECEPTACLE/ANGLE ADAPTER

45-47003-P80

SPECIFICATIONS

600 A

600 VAC

IP66/IP67

Rated Current (A)	600 A
Rated Voltage (V)	600 VAC
Contact Configuration	L3
Auxiliary Contacts	+2 AUX
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	IP 66/67
Short Circuit Rating	30 kA - WITHSTAND
Impact Rating	IK08
Material	POLY
Product Color	BLACK
Minimum Operating Temperature	-15F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	2/0 AWG - 777 MCM LUG TERMINAL
Applicable Standards	cCSAus C22.2 No. 182.1-07
Accessory Size	S
Base Drawing Number	45-4700x.PDF
Catalog	meltric-catalog-sp-en.pdf