



SP RECEPTACLE

45-4400M

SPECIFICATIONS

700 A
1500 VDC
IP66/IP67

| | |
|---|---|
| Rated Current (A) | 700 A |
| Rated Voltage (V) | 1500 VDC |
| Contact Configuration | NEGATIVE |
| Auxiliary Contacts | +2 AUX |
| Ratings Information | NON-CURRENT INTERRUPTING |
| Environmental Rating | IP 66/67 |
| Impact Rating | IK08 |
| Material | POLY |
| Product Color | BLACK |
| Minimum Operating Temperature | -40F -40C |
| Maximum Operating Temperature | 140F 60C |
| Wiring Capacity - Phase Contacts | 1/0 AWG - 777 MCM LUG TERMINAL |
| Accessory Size | S |
| Base Drawing Number | 45-4400x-p80.pdf |
| Catalog | meltric-catalog-sp-en.pdf |