



SP INLET

45-4800P

SPECIFICATIONS

700 A
1500 VDC
IP66/IP67

Rated Current (A)	700 A
Rated Voltage (V)	1500 VDC
Contact Configuration	POSITIVE
Auxiliary Contacts	+2 AUX
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	IP 66/67
Impact Rating	IK08
Material	POLY
Product Color	BLACK
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	1/0 AWG - 777 MCM LUG TERMINAL
Accessory Size	S
Base Drawing Number	45-4800x-p80.pdf
Catalog	meltric-catalog-sp-en.pdf