



HANDLE

47-3A013-225

SPECIFICATIONS

IP66/IP67

Environmental Rating	IP 66/67
Material	METAL
Metal Type	ALUMINUM PAINTED
Product Color	GRAY
Cable Range	2.125-2.250"
Interior Volume	307 cu in
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Accessory Size	F
Base Drawing Number	47-3a013-xxx.PDF