



DSN20 RECEPTACLE

63-14122-K16-843-NC

SPECIFICATIONS

20 A

208 VAC

Type 4X & IP69

1 hp

Rated Current (A)	20 A
Rated Voltage (V)	208 VAC
Horsepower Rating	1 hp
Contact Configuration	2P+G
Auxiliary Contacts	NO AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG – 12 AWG SCREW TERMINAL
Applicable Standards	UL 1682 UL 2682 cCSAus C22.2 No. 182.1-13
Option(1)	PADLOCK PAWL
Option(2)	NORMALLY CLOSED LID
Accessory Size	1
Base Drawing Number	63-14xxx.PDF
Catalog	meltric-catalog-dsn20-en.pdf