



DSN60 RECEPTACLE

63-64043-972-270

SPECIFICATIONS

60 A
 480 VAC
 Type 4X & IP69
 20 hp

Rated Current (A)	60 A
Rated Voltage (V)	480 VAC
Horsepower Rating	20 hp
Contact Configuration	3P+G
Auxiliary Contacts	+2 AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG – 4 AWG SCREW TERMINAL
Option(1)	AUXILIARY SWITCH
Accessory Size	3
Base Drawing Number	63-64xxx.pdf
Catalog	meltric-catalog-dsn60-en.pdf