



DSN60 RECEPTACLE

63-64143-352

SPECIFICATIONS

60 A

600 VAC

Type 4X & IP69

20 hp

Rated Current (A)	60 A
Rated Voltage (V)	600 VAC
Horsepower Rating	20 hp
Contact Configuration	3P+G
Auxiliary Contacts	NO AUX
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG - 4 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 182.1-13
Option(1)	STRAIGHT INSERTION
Accessory Size	3
Base Drawing Number	63-64xxx.pdf
Catalog	meltric-catalog-dsn60-en.pdf