



DSN100 RECEPTACLE

63-84143-264

SPECIFICATIONS

100 A

600 VAC

Type 4X & IP69

50 hp

Rated Current (A)	100 A
Rated Voltage (V)	600 VAC
Horsepower Rating	50 hp
Contact Configuration	3P+G
Auxiliary Contacts	+4 AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	10 AWG - 2 AWG SCREW TERMINAL
Applicable Standards	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	4
Base Drawing Number	63-84xxx.pdf
Catalog	meltric-catalog-dsn100-en.pdf