



DSN150 HAZ INLET

66-98142-HAZ

SPECIFICATIONS

150 A
 600 VAC
 Type 4X
 25 hp

Rated Current (A)	150 A
Rated Voltage (V)	600 VAC
Horsepower Rating	25 hp
Contact Configuration	2P+G
Auxiliary Contacts	NO AUX
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	Type 4X IP 66/67
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK10
Material	METAL
Metal Type	ZAMAK
Product Color	METAL
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	104F 40C
Wiring Capacity - Phase Contacts	4 AWG – 2/0 AWG SCREW TERMINAL
Hazardous Ratings	Class I Zone IIC Class I Div 2 Groups A,B,C,D T6
Applicable Standards	cCSAus C22.2 No. 182.1-07
Accessory Size	5
Base Drawing Number	66-98xxx-xxx-haz.pdf
Catalog	meltric-catalog-zone2-dsn150-en.pdf