



DSN150 HAZ INLET

66-98147-HAZ

SPECIFICATIONS

150 A
 347/600 VAC
 Type 4X
 NA/75 hp

| | |
|---|---|
| Rated Current (A) | 150 A |
| Rated Voltage (V) | 347/600 VAC |
| Horsepower Rating | NA/75 hp |
| Contact Configuration | 3P+N+G |
| Auxiliary Contacts | NO AUX |
| Ratings Information | NON-CURRENT INTERRUPTING |
| Environmental Rating | Type 4X IP 66/67 |
| Short Circuit Rating | 100 kA - CLOSE & WITHSTAND |
| Impact Rating | IK10 |
| Material | METAL |
| Metal Type | ZAMAK |
| Product Color | METAL |
| Minimum Operating Temperature | -40F -40C |
| Maximum Operating Temperature | 104F 40C |
| Wiring Capacity - Phase Contacts | 4 AWG – 2/0 AWG SCREW TERMINAL |
| Hazardous Ratings | Class I Zone IIC Class I Div 2 Groups A,B,C,D T6 |
| Applicable Standards | cCSAus C22.2 No. 182.1-07 |
| Accessory Size | 5 |
| Base Drawing Number | 66-98xxx-xxx-haz.pdf |
| Catalog | meltric-catalog-zone2-dsn150-en.pdf |