



DSN100 RECEPTACLE

69-84043-375

SPECIFICATIONS

100 A
 480 VAC
 Type 4X & IP69
 50 hp

| | |
|---|---|
| Rated Current (A) | 100 A |
| Rated Voltage (V) | 480 VAC |
| Horsepower Rating | 50 hp |
| Contact Configuration | 3P+G |
| Auxiliary Contacts | NO AUX |
| Ratings Information | SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH |
| Environmental Rating | Type 4X IP 66/67 IP 69 |
| Short Circuit Rating | 100 kA - CLOSE & WITHSTAND |
| Impact Rating | IK09 |
| Material | METAL |
| Metal Type | ALUMINUM |
| Product Color | BLUE |
| Minimum Operating Temperature | -40F -40C |
| Maximum Operating Temperature | 140F 60C |
| Wiring Capacity - Phase Contacts | 10 AWG – 2 AWG SCREW TERMINAL |
| Applicable Standards | UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13 |
| Option(1) | MUSHROOM PAWL |
| Accessory Size | 4 |
| Base Drawing Number | 63-84xxx.pdf |
| Catalog | meltric-catalog-dsn100-en.pdf |