



# DSN100 RECEPTACLE

69-84143

## SPECIFICATIONS

100 A  
 600 VAC  
 Type 4X & IP69  
 50 hp

<b>Rated Current (A)</b>	100 A
<b>Rated Voltage (V)</b>	600 VAC
<b>Horsepower Rating</b>	50 hp
<b>Contact Configuration</b>	3P+G
<b>Auxiliary Contacts</b>	NO AUX
<b>Ratings Information</b>	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
<b>Environmental Rating</b>	Type 4X IP 66/67 IP 69
<b>Short Circuit Rating</b>	100 kA - CLOSE & WITHSTAND
<b>Impact Rating</b>	IK09
<b>Material</b>	METAL
<b>Metal Type</b>	ALUMINUM
<b>Product Color</b>	BLUE
<b>Minimum Operating Temperature</b>	-40F -40C
<b>Maximum Operating Temperature</b>	140F 60C
<b>Wiring Capacity - Phase Contacts</b>	10 AWG - 2 AWG SCREW TERMINAL
<b>Applicable Standards</b>	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
<b>Accessory Size</b>	4
<b>Base Drawing Number</b>	<a href="#">69-84xxx.pdf</a>
<b>Catalog</b>	<a href="#">meltric-catalog-dsn100-en.pdf</a>