



DSN100 INLET

69-88043-270

SPECIFICATIONS

100 A
 480 VAC
 Type 4X & IP69
 50 hp

Rated Current (A)	100 A
Rated Voltage (V)	480 VAC
Horsepower Rating	50 hp
Contact Configuration	3P+G
Auxiliary Contacts	NO AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	METAL
Metal Type	ALUMINUM
Product Color	METAL
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	10 AWG – 2 AWG SCREW TERMINAL
Option(1)	AUXILIARY SWITCH
Accessory Size	4
Base Drawing Number	69-88xxx.pdf
Catalog	meltric-catalog-dsn100-en.pdf