



# Cable Glands

## PG Threads Cable Glands



Clamping Cable Glands | CRSS Series | PG Threads | IP55 Rating

Part Number	Diameter Range mm (inches)	Thread Type
CRSS-09	7 - 10 (0.255 - 0.374)	PG 9
CRSS-11	8 - 12 (0.295 - 0.452)	PG 11
CRSS-13.5	9 - 13 (0.334 - 0.531)	PG 13.5
CRSS-16	10 - 15 (0.374 - 0.591)	PG 16
CRSS-21	12.5 - 19 (0.472 - 0.748)	PG 21
CRSS-29	19 - 27 (0.728 - 1.063)	PG 29
CRSS-36	26 - 33 (1.00 - 1.30)	PG 36
CRSS-42	30.5 - 39 (1.18 - 1.54)	PG 42
CRSS-48	35 - 45 (1.35 - 1.77)	PG 48

### CRSS Series

Nickel Plated Brass Cable Gland with self-centering double saddle clamps. The seal is achieved with a neoprene sealing ring (with multiple perforations to accommodate a wide range of diameters). Brass Nuts and O-Rings for these must be ordered separately. Protection to IP 55.

