



1 1/8" MIN Series Size III Accessories

9, 10, 12 & 19 Conductor MIN Series Size III Accessory Cables



100' Cables | Raw Cable Spools

# of Conductors	Color Code	Wire AWG	Voltage Rating	Features	Part Number	
					100' Cable	Spool
9	North American 1. Orange 6. Red 2. Blue 7. Green/Yellow 3. Red/Black 8. White/Black 4. Green/Black 9. Black 5. White	18 AWG	300V	Yellow PVC AWM 9.1mm OD (0.36" OD)	MIN-9CBLX-C	10H0001-*
		18 AWG	300V	Yellow PUR AWM 9.1mm OD (0.36" OD)	MINP-9CBLX-C	10HP001-*
10	North American 1. Orange 6. Orange/Black 2. Blue 7. Red 3. White/Black 8. Green/Yellow 4. Red/Black 9. Black 5. Green/Black 10. White	18 AWG	300V	Yellow PVC AWM 10.1mm OD (0.40" OD)	MIN-10CBLX-C	10J0001-*
		18 AWG	300V	Yellow PUR AWM 10.1mm OD (0.40" OD)	MINP-10CBLX-C	10JP001-*
12	North American 1. Orange 7. Blue/Black 2. Blue 8. Black/White 3. White/Black 9. Green/Yellow 4. Red/Black 10. Red 5. Green/Black 11. White 6. Orange/Black 12. Black	18 AWG	300V	Yellow PVC AWM 10.5mm OD (0.41" OD)	MIN-12CBLX-C	10K0001-*
		18 AWG	300V	Yellow PUR AWM 10.5mm OD (0.41" OD)	MINP-12CBLX-C	10KP001-*
19	1. Violet 11. Black 2. Red 12. Green/Yellow*** 3. Gray 13. Yellow/Brown 4. Red/Blue 14. Brown/Green 5. Blue*** 15. White 6. Green 16. Yellow 7. Brown*** 17. Pink 8. White/Green 18. Gray/Brown 9. White/Yellow 19. Gray/Pink 10. White/Gray	3 x 18 AWG & 16 x 22 AWG	300V	Yellow PUR UL 20233 With Foil Shield 11mm OD (0.43" OD)	MINP-19CBL-C	54RMP01-*

C
MIN Series Size III Cordsets

* Standard raw spool lengths are 0250, 0500, 0750 & 1000 feet. Consult factory for other lengths.

*** For the 19 Pin, blue, brown, and green/Yellow wires are 18 AWG.

Cable Construction subject to change without notice.

Length in feet. Standard cable length is 100 feet. Consult factory for other lengths.