



# MCV Series Accessories

12, 16, 17 & 19 Conductor MCV Series Accessory Cables



100' Cables | Raw Cable Spools

E

M16, M23 & M27 Series

# of Conductors	Color Code	Wire AWG	Voltage Rating	Features	Part Number	
					100' Cable	Spool
12	Black Numbered Wires #1-11 Green/Yellow #12	18 AWG	300V	Black TPE AWM 9.9mm OD (0.39" OD)	MCV-12CBLX-C	10KWXB2-*
	<b>Brown***</b> Gray Brown/White    Pink <b>Blue***</b> Red White            Black Green            Violet Yellow <b>Green/Yellow***</b>	18 & 22 AWG	300V	Black PUR AWM with Foil Shield 8.1mm OD (0.31" OD)	MCVP-12CBL-C	54KMP01-*
				Black TPE AWM with Foil Shield 8.1mm OD (0.31" OD)	MCVW-12CBL-C	54KMW01-*
16	Black Numbered Wires #1-15 Green/Yellow #16	18 AWG	150V	Black PVC AWM 13.6mm OD (0.53" OD)	MCV-16CBLX-C	54PXB1-*
	White            Black Brown           Violet Green            Gray/Pink Yellow           Red/Blue Gray            White/Green Pink            Brown/Green Blue            White/Yellow Red            Yellow/Brown	18 AWG	150V	Black PVC AWM 12.1mm OD (0.48" OD)	MCV-16CBLX-C-C010	54PXB02-*
17	Black Numbered Wires #1-16 Green/Yellow #17	18 AWG	150V	Black PVC AWM 13.6mm OD (0.53" OD)	MCV-17CBLX-C	54PXB1-*
	White            Violet Brown           Gray/Pink Green            Red/Blue Yellow           White/Green Gray            Brown/Green Pink            White/Yellow Blue            Yellow/Brown Red            White/Gray Black	18 AWG	150V	Black PVC AWM 12.1mm OD (0.48" OD)	MCV-17CBLX-C-C010	54PXB02-*
19	Violet            Black Red            Green/Yellow Gray            Yellow/Brown Red/Blue       Brown/Green Green           White Blue            Yellow Gray/Pink      Pink White/Green    Gray/Brown White/Yellow   Brown White/Gray	18 AWG	150V	Black PVC AWM 13.6mm OD (0.53" OD)	MCV-19CBLX-C	10RXB02-*
	Violet            Black Red <b>Green/Yellow***</b> Gray            Yellow/Brown Red/Blue       Brown/Green Green           White <b>Blue***</b> Yellow Gray/Pink      Pink White/Green    Gray/Brown White/Yellow <b>Brown***</b> White/Gray	18 & 22 AWG	150V	Black PUR AWM 9.9mm OD (0.43" OD)	MCVP-19CBL-C	54RMP01-*
Black TPE AWM 9.4mm OD (0.38" OD)				MCVWF-19CBL-C	54REB01-*	

\* Standard raw spool lengths are 0250, 0500, 0750 & 1000 feet. Consult factory for other lengths.

\*\*\* Blue, Brown and Green/Yellow wires are 18AWG.

Cable Construction subject to change without notice.

Lengths in feet. Standard cable length is 100 feet. Consult factory for other lengths.